



Benchtop Hardness testers

NauMetrics PMI Postbus 540 7550 AM Hengelo T: 0031 (0) 74 3490022 F: 0031 (0) 84 0037042 info@naumetrics.nl www.naumetrics.nl



Inhoudsopgave:

Benchtop Hardnesstesters

Digital Rockwell testers	
KHR-450/500	Pag. 3
KHR-300/310/320	Pag. 6
Digital Brinell Hardness testers	
KHB-3000A	Pag. 9
KHB-3000E	Pag. 12
Digital Vickers Hardness testers	
THV-5MD/	Pag.14
THV-10MD	-



Rockwell/Superficial Rockwell hardness tester



Digital Superficial Hardness tester KHR-450

Digital Hardnesstester KHR-500

KHR-450 can be used directly to measure Rockwell Superficial hardness and plastic hardness, and it can change the value of Rockwell superficial hardness such as HR15N, HR30N, HR 45N, HR15T, HR30T and HR45T scale into HV, HB, ob and HK value.

KHR-500 can be used directly to measure Rockwell hardness and plastic Rockwell hardness, and it can change the value of Rockwell hardness into HB, HV, HLD, HK and σ b value.

Provided with many features such as

- High Measuring Precision
- Wide measuring range,
- Automatic test force
- Changing according the scales,
- Automatic main test force loading/unloading,
- Measuring results digitally display and automatic printing,
- Communicating with external computer and etc.,
- The tester is suitable for the hardness testing of carbon steel, alloy steel, cast iron, non-ferrous metal, engineering plastic and etc.



	KHR-500	KHR-450	
Preload	98.1N (10kgf)	29.4N (3kgf)	
Test force	588.4N(60kgf), 980.7N	147.1N(15kgf),	
	(100kgf), 1471N(150kgf)	294.3N(30kgf),	
		441.3N(45kgf)	
Scales	HRA, HRB, HRC, HRD,	HR15N,HR30N,HR45N,	
	HRE, HRF, HRG, HRH,	HR15T,HR30T,HR45T,	
	HRK, HRL, HRM, HRP,	HR15W,HR30W,HR45W,	
	HRR, HRS, HRV	HR15X,HR30X,HR45X,	
		HR15Y,HR30Y,HR45Y	
Load cycle	3~8s	3~8s	
Load dwell duration	2~50s	2~50s	
Resolution	0.1HR	0.1HR	
Display	High definition backlight LCD	High definition backlightLCD	
Operation	Menu selectable, Membrane	Menu selectable, Membrane keypad	
	keypad		
Auxiliary functions	Upper/lower limits setting&	Upper/lower limits setting&	
	alarming,	alarming,	
	Data statistics, Avg., Max.,	Data statistics, Avg., Max., Min., S, R,	
	Min., S, R,	Scale conversion, HV, HB, σ_b ,	
	Scale conversion, HV, HB,	Curved surface correcting automatically	
	σ _b ,		
	Curved surface correcting		
	automatically		
Data output	RS-232/USB data output to	RS-232/USB data output to printer or PC	
	printer or PC		
Memory	Max 500 items of test results	Max 500 items of test results stored automatically	
	stored automatically		
Testing Space	200mm in vertical,165mmin	200mm in vertical,165mmin horizontal	
	horizontal		
Dimensions	550mm×200mm×720mm	550mm×200mm×720mm	
Power supply	AC, 110V, 50∼60Hz,4A	AC, 110V/220V, 50~60Hz,4A	
Net weight	100kg	90kg	



<i>چ</i>	KHR-500↩	KHR-450₽
Host machine	40	40
Standard hardness block for A scale	40	¢+
Standard hardness block for B scale?	40	¢,
Standard hardness block for C scale	40	\$
Standard hardness block for HR30N scale∉	C4	40
Standard hardness block for HR30T scale₽	ę	40
1/16" steel ball indenter₽	40	40
120°cone diamond indenter∻	40	40
Mounting screw for indenter ×2+	40	40
Round plane anvil₽	40	40
"V" shape anvil↩	40	40
Power supply wire	40	40
Screwdriver for indenter mounting₽	40	40
Dust cover@	40	40



Advanced Nose-Type Digital Rockwell Testers



KHR-300 Rockwell hardnestester

KHR-310 Superficial Rockwell hardnesstester

KHR-320 TWIN Rockwell hardnesstester

- Horizontal Protruding Indenter Design, suitable also for internal and external testing.
- Testing on Surfaces difficult to reach. Testing internal surface of rings and tubes with diameters over 23mm.
- Modern design with Titanium metallic Silver finish
- Provided with many features such as high measuring precision, wide measuring range
- The tester is suitable for testing of carbon steel, alloy steel, cast iron, non-ferrous metal.
- Automatic load cycle. The loading, dwell, unloading process of the main test force are controlled exactly to meet standard.
- Measuring results digitally displaying and can be printed, or transmitted to external computer automatically by USB or RS-232 data output port.
- Test value can be transformed to the value of HB, HV, HK and ob value.
- The tester meets all following standards such as ISO 6508-2, ASTM E18.



	KHR-300	KHR-310	KHR-320
Preload	98.1N (10kgf)	29.4N (3kgf)	29.4N (3 kgf)
			98.1N (10 kgf)
Total test force	588.4N (60kgf), 980.7N	147.1N(15kgf), 294.3N	147.1N(15kgf), 294.3N
	(100kgf), 1471N (150kgf)	(30kgf), 441.3N(45kgf)	(30kgf), 441.3N(45kgf),
			588.4N (60kgf), 980.7N
			(100kgf), 1471N (150kgf)
Scales	HRA, HRB, HRC, HRD,	HR15N, HR30N, HR45N,	HR15N, HR30N, HR45N,
	HRE, HRF, HRG, HRH,	HR15T, HR30T, HR45T,	HR15T, HR30T, HR45T,
	HRK, HRL, HRM, HRP,	HR15W, HR30W, HR45W,	HR15W, HR30W, HR45W,
	HRR, HRS, HRV	HR15X, HR30X, HR45X,	HR15X,
		HR15Y, HR30Y, HR45Y	HR30X, HR45X, HR15Y,
			HR30Y, HR45Y
			HRA, HRB, HRC,
			HRD, HRE, HRF,
			HRG, HRH, HRK,
			HRL, HRM, HRP,
			HRR, HRS, HR∨
Load dwell dura-	$2{\sim}50$ s, can be set and stored		
tion			
Resolution	0.1HR		



Display	High definition backlight LCD			
Operation	Menu selectable, Membrane keypad			
Upper/lower lim-	\checkmark	\checkmark	\checkmark	
its setting &				
alarming				
Data statistics	Avg	., Max., Min., S, R available		
Curved surface	\checkmark	\checkmark	\checkmark	
correcting auto-				
matically				
Memory	Max 500 item	ns of test results stored auto	matically	
Data output	RS-232 to micro printer, USB port to external PC			
Testing space	240mm in vertical,155mmin horizontal			
Dimensions	720mm×220mm×800mm			
Power supply	AC, 220V/110V, 50~60Hz,4A			
Net weight	120kg	110kg	130kg	



Automatic Brinell Hardnesstester KHB-3000A



Contact to desktop PC or Contact to laptop PC.

The Brinell hardness testing creates the largest indentation comparing all other hardness testing methods. It is able to reflect the comprehensive features of the material, and is unaffected by the microstructure and Inhomogeneous of the specimen. So with its high precision it is widely used in industries such as metallurgy, forging, casting, unhardened steel and nonferrous metals, as well as in the laboratories, universities, and scientific research institutes. KHB-3000A Tester conforms to: ISO6506 Metallic Materials-Brinell Hardness Test ASTM E-10 Test Method for Brinell Hardness of Metallic Materials.

Specification: Innovative closed-loop technology. The tester incorporates the latest load cell technology. The test load is applied via a closed-loop control unit with a load cell, a DC motor and an electronic measurement and control unit. The result is highly accurate measurements at all test loads up to 0.5%. The common load overshoot or undershoot as known from traditional dead weight, or open-loop, systems is eliminated. The absence of mechanical weights not only eliminates friction problems but also makes the equipment less sensitive to misalignments caused by vibrations. The whole weight of the tester is 50% less than the traditional dead weights type tester. Test load selection by keyboard and LCD screen. No need of handling heavy weights or cleaning the messy oil. Fully automatic test cycles. The hardness Tester features a fully automatic test cycle, load application, holding, unloading, is performed fully automatically. This greatly improves reproducibility of test results since operator influence is eliminated. Selectable dwell times by screen. The indenter, load, and other test information are showing clearly on the large LCD screen. The directions for 0.102F/D2 ratios selecting according to the materials and hardness range can be showing on the screen.





Equipped with the special Brinell indention measure system, which can measure the Brinell indention accurate, quick and reliable. It is a new measuring method by using CCD camera to capture the indention image, instead of reading diameter from optical microscope by operator then calculating the test value. The KHB-3000A tester can connect any PC with USB port and run the SPC software, then the special software supplies an easy operation as following.



Both single testing and batch testing mode are available with tolerance setting, distinguishing and alarming statistic values such as Max, Min, Avg, R and S are available to convert test result to other scales, such as HRC,HRB,HRA,HV, mb.





Loads: 3000kgf (29400N), 1500kgf (14700N), 1000kgf (9800N), 750kgf (7355N) ,+

500Kgf (4900N), 250Kgf (2452N), 187.5Kgf (1839N), 125Kgf (1226N), e

100Kgf (980N), 62.5Kgf (612.9N)+

Load dwell duration: 2s~99s, can be set and stored 🖉

Tungsten Carbide Ball indenter. 10mm.

Measuring range: 3.18HBW~658HBW+

Accuracy of indention measureing: ±0.5%+

Accuracy of Brinell Hardness Value:

Hardness Range(HBW)₽	Error (%)₽	Repeatability(%)₽
≤ 125₽	± 2.5₽	≤3.0₽
125 <hbw≤225₽< td=""><td>± 2.040</td><td>≤2.5 ₽</td></hbw≤225₽<>	± 2.040	≤2.5 ₽
> 225 +2	±1.5 ₽	≤2.0₽
Max measurable height 200 mm	¢,	

Max measurable depth: 140 mm₽

Dimensions: 530mm×260mm×750mme

Power supply: 220/110 V, 50/60 Hz, 4Ae

Weight: 120kg₽

Standard blocks: 125-350HBW10/3000, 125-350HBW10/1000+

Standar	rd conf	iguration.	
Host machine₽	10	Software disc.	143
Standard block125-350HBW10/3000+2	10	USB Key₽	147
Standard block125-350HBW10/1000+2	10	USB Cable₽	143
Φ10mm Tungsten Carbide Ball indenter+	10	Power supply wiree	143
Mounting screws for indenter₽	10	Dust cover₽	143
Screwdriver for indenter mounting#	10	Flat anvil, 80mm×185mm@	143
Option	al acce	essories	
"V" shape anvil, 80mm×185mm₽		Standard blocks of other v	/alue₽
Φ5mm Tungsten Carbide Ball indenter₽		Φ2.5mm Tungsten Carbide Ball indenter	
Φ10mm Tungsten Carbide Ball₀		Φ5mm Tungsten Carbide	Ball₽
Φ2.5mm Tungsten Carbide Ball₽		Ca Ca	



Electronic Brinell Hardnesstester KHB-3000E



The Brinell hardness testing creates the largest indentation comparing all other hardness testing methods. It is able to reflect the comprehensive features of the material, and is unaffected by the microstructure and inhomogeneous of the specimen. So with its high precision it is widely used in industries such as metallurgy, forging, casting, unhardened steel and nonferrous metals, as well as in the laboratories, universities, and scientific research institutes.

KHB-3000E Tester conforms to:

- ISO6506 Metallic Materials-Brinell Hardness Test
- ASTM E-10 Test Method for Brinell Hardness of Metallic Materials

Specification:

- Innovative closed-loop technology. The tester incorporates the latest load cell technology. The test load is applied via
 a closed-loop control unit with a load cell, a DC motor and an electronic measurement and control unit. The result is
 highly accurate measurements at all test loads up to 0.5%. The common load overshoot or undershoot as known from
 traditional dead weight, or open-loop, systems is eliminated. The absence of mechanical weights not only eliminates
 friction problems but also makes the equipment less sensitive to misalignments caused by vibrations.
- The whole weight of the tester is 50% less than the traditional dead weights type tester.
- Test load selection by keyboard and LCD screen. No need of handling heavy weights or cleaning the messy oil.
- Fully automatic test cycles. The hardness Tester features a fully automatic test cycle, load application, holding, unloading, is performed fully automatically. This greatly improves reproducibility of test results since operator influence is eliminated.
- Selectable dwell times by screen. The indenter, load, and other test information are shown clearly on the large LCD screen.
- The directions for 0.102F/D2 ratios selecting according to the materials and hardness range can be showing on the screen.
- 20X Microscope with LED lighting source make the indention more distinguishable and improving the measure accurate.



Loads: 3000kgf (29400N), 1500Kgf (14700N), 1000Kgf (9800N), 750Kgf (7355N) ,+

500Kgf (4900N), 250Kgf (2452N), 187.5Kgf (1839N), 125Kgf (1226N),4

100Kgf (980N), 62.5Kgf (612.9N)-

Load dwell duration: 2s~99s, can be set and stored 🤟

Tungsten Carbide Ball indenter. 10mm,4

Measuring range: 3.18HBW~658HBW@

Magnification of the microscope: 20Xe

Resolution capability of the microscope: 0.005mm 🤟

Accuracy of Brinell Hardness Value:

Hardness Range(HBW)₽	Error (%)₽	Repeatability(%)₽			
≤ 125₽	± 3.0+	≤3.0₽			
125 <hbw≤225₽< td=""><td>± 2.5₽</td><td>≤2.5 ₽</td></hbw≤225₽<>	± 2.5₽	≤2.5 ₽			
> 225 +	±2.0 +	≤2.0₽			
Max measurable height 230 mm+					
Max measurable depth: 140 mm.					
Dimensions: 530mm×260mm×750m	nm₽				

Power supply: 220/110 ∨, 50/60 Hz, 4A₽

Weight: 120kg@

Standard blocks: 125-350HBW10/3000, 125-350HBW10/1000+

Standard configuratione			
Host machine₽	1*	Flat anvile	147
Standard block125-350HBW10/3000₽	1₽	"∨" shape anvile	10
Standard block125-350HBW10/1000₽	1₽	20X microscope₽	10
Φ10mm Tungsten Carbide Ball indenter∉ 1₽		Power supply wire₽	10
Mounting screws for indentere	1₽	Dust cover₽	10
Screwdriver for indenter mounting₽	1₽	چ.	ę
Option	nal acce	ssories;e	
Standard blocks of other value#		Φ2.5mm Tungsten Carbi	de Ball₽
Φ5mm Tungsten Carbide Ball indenter₽		Φ2.5mm Tungsten Carbide B	all indenter@
Φ10mm Tungsten Carbide Balle Φ5mm Tungsten Carbide Balle		e Ball₽	



Digital Automatic Turret Vickers

Hardnesstester

THV-5MD

THV-10MD

Model THV-5MD/-10MD Digital Automatic Turret Vickers hardness tester with large screen LCD display, use the menu interface type structure, can be in operation panel choose hardness HV or rod HK, test of hardness value, automatic input, automatic display. For all kinds of hardness value mutual conversion, and the testing result is automatic storage, processing, printing, with RS-232 interface, and computer online. The machine is digital, with a high degree of automation. Hardness value error can be modified through software input; hardness value more accurate meets the requirement.

Model THV-5MD/-10MD Digital Automatic Turret Vickers hardness tester with digital display when the pressure head and the objective to switch to each other, the test point to be automatic positioning precision.

Model	THV-5MD		
Min measuring unit	0.0625µm		
Test force	0.3Kgf(2.94N) 、 0.5Kgf(4.9N) 、 1.0Kgf(9.8N) 、 2.0Kgf(19.6N) 、 3.0Kgf(29.4N)、5Kgf(49.0N)		
Max Height of Specimen	160mm		
Distance of Indenter to outer wall	135mm		
Hardness measuring range	8~2900HV		
method of testing force applied	Automatic loading, unloading testing force		
Test microscope magnification	200X(Measuring), 100X (observation)		
Duration time	0~60s		
Overall Dimension	520*190*650mm		
Power supply	AC220V+5%, 50-60Hz		
Net weight	About 40Kg		

Technical Specifications:



Technical Specifications:

Model	THV-10MD
Min measuring unit	0.0625µm
Test force	0.3Kgf(2.94N) 、 0.5Kgf(4.9N) 、 1.0Kgf(9.8N) 、 2.0Kgf(19.6N) 、 3.0Kgf(29.4N)、5Kgf(49.0N), 10Kgf(98.0)
Max Height of Specimen	160mm
Distance of Indenter to outer wall	135mm
Net weight	About 40Kg
Power supply	AC220V+5%, 50-60Hz
Net weight	About 40Kg
Overall Dimension	520*190*650mm
Hardness measuring range	8~2900HV
method of testing force applied	Automatic loading, unloading testing force
Test microscope magnification	200X(Measuring), 100X (observation)
Duration time	0~60s

Standard Accessories:

Item	Quantity	Item	Quantity
Weight	3	Vickers hardness block	2
"V" shaped Testing Table	1	Fuse(2A)	2
Circular testing table	1	Power cable	1
Large Testing Table	1	Product Certificate	1
Objective 10X	1	Printer manual, Manual	Each 1